

**VPK (blanking plug in plastic)  
VP 16-K54**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Type	VP 16-K54
Order No.	<a href="#">0295060000</a>
Version	VPK (blanking plug in plastic), Blanking plug, PG 16, 5 mm, IP65, Polyamid 6 (PA6 - GF30)
GTIN (EAN)	4008 190170479
Qty.	100 pc(s).

## VPK (blanking plug in plastic) VP 16-K54

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Length	10 mm	Length (inches)	0.394 inch
Net weight	1.8 g		

### General information

Material	Polyamid 6 (PA6 - GF30)	Cable glands	PG
External thread	PG 16	Length of thread	5 mm
Protection degree	IP54	Protection degree with GWDR	IP65
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Head diameter	27 mm	UL 94 flammability rating	V-2
Halogen	No		

### Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-33
eClass 10.0	27-14-44-25	UNSPSC	30-21-18-01

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**VPK (blanking plug in plastic)  
VP 16-K54**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

