

**VPMS (blanking plug in brass)
VP 21-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP 21-MS65
Order No.	0295 100000
Version	VPMS (blanking plug in brass), Blanking plug, PG 21, 6 mm, Brass, nickel-plated
GTIN (EAN)	4008 190128593
Qty.	50 pc(s).

Creation date August 21, 2020 8:09:32 PM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

Data sheet

VPMS (blanking plug in brass) VP 21-MS65

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	10 mm	Length (inches)	0.394 inch
Height	10 mm	Height (inches)	0.394 inch
Net weight	23.62 g	Diameter	32 mm

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General information

Material	Brass, nickel-plated	Cable glands	PG
External thread	PG 21	Length of thread	6 mm
Protection degree	IP68 - 5 bar (30 min.)	Operating temperature range, min.	-40 °C
Operating temperature range, max.	100 °C	Head diameter	32 mm
Halogen	No	O-Ring	NBR
Sealing	NBR		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-33
eClass 10.0	27-14-44-25	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**VPMS (blanking plug in brass)
VP 21-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

