

**SAK Series
AD 3 SAK6N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	AD 3 SAK6N
Order No.	0297700000
Version	SAK Series, cover plate, yellow, 24 mm
GTIN (EAN)	4008 190086787
Qty.	50 pc(s).

**SAK Series
AD 3 SAK6N**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	24 mm	Width (inches)	0.945 inch
Height	25 mm	Height (inches)	0.984 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	0.76 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PVC	Colour	yellow
UL 94 flammability rating	V-2		

System specifications

Version	End and intermediate plate
---------	----------------------------

Additional technical data

Installation advice	Direct mounting	Snap-on	No
---------------------	-----------------	---------	----

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-27

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks