

**SAK Series
AH 46 SAKG46**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	AH 46 SAKG46
Order No.	0326960000
Version	SAK Series, Hood, beige, 46 mm
GTIN (EAN)	4008190174712
Qty.	5 pc(s).

SAK Series
AH 46 SAKG46

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	46 mm	Width (inches)	1.811 inch
Height	196 mm	Height (inches)	7.717 inch
Depth	78 mm	Depth (inches)	3.071 inch
Net weight	81.04 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

System specifications

Version	Hood
---------	------

Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-27

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks