

**SAK Series
BS 25 IH/GE SAKT1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | |
|------------|----------------------------|
| Type | BS 25 IH/GE SAKT1 |
| Order No. | 0335700000 |
| Version | SAK Series, Set of fixings |
| GTIN (EAN) | 4008190189235 |
| Qty. | 50 pc(s). |

**SAK Series
BS 25 IH/GE SAKT1**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Width | 5.5 mm | Width (inches) | 0.217 inch |
| Height | 5.5 mm | Height (inches) | 0.217 inch |
| Depth | 28.7 mm | Depth (inches) | 1.13 inch |
| Net weight | 1.78 g | Diameter | 3 mm |

Temperatures

| | | | |
|---------------------------|---------------|---------------------------|-------|
| Storage temperature, max. | 40 °C | Storage temperature, min. | 10 °C |
| Storage temperature | 10 °C...40 °C | | |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Material data

| | | | |
|----------|-------|--------|--------|
| Material | Steel | Colour | yellow |
|----------|-------|--------|--------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | Type of mounting | when screwed in |

Dimensions

| | |
|----------|------|
| Diameter | 3 mm |
|----------|------|

Classifications

| | | | |
|-------------|-------------|------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| eClass 9.0 | 27-14-11-92 | eClass 9.1 | 27-14-11-92 |
| eClass 10.0 | 27-14-11-92 | UNSPSC | 30-21-18-11 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |
| User Documentation | StorageConditionsTerminalBlocks |