

**SAK Series  
Q 4 SAK16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Product image**



Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	Q 4 SAK16
Order No.	<a href="#">0457700000</a>
Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 4
GTIN (EAN)	4008 190070823
Qty.	50 pc(s).

**SAK Series**  
**Q 4 SAK16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	41.7 mm	Width (inches)	1.642 inch
Height	6 mm	Height (inches)	0.236 inch
Depth	20.5 mm	Depth (inches)	0.807 inch
Net weight	12.62 g		

**Temperatures**

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Material data**

Material	CuSn	Colour	grey
----------	------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Dimensions**

Pitch in mm (P)	6 mm
-----------------	------

**Rating data**

Rated current	76 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN_WSCAD</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>