

**Accessories**  
**IK 35/ZB35 BL****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image****Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

**General ordering data**

Type	IK 35/ZB35 BL
Order No.	<a href="#">0502780000</a>
Version	Accessories, Special terminal, Rated cross-section: PA, blue, Busbar
GTIN (EAN)	4008 190141455
Qty.	50 pc(s).

**Accessories**  
**IK 35/ZB35 BL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	14 mm	Width (inches)	0.551 inch
Height	32 mm	Height (inches)	1.26 inch
Depth	8.6 mm	Depth (inches)	0.339 inch
Net weight	1.34 g		

**Temperatures**

Operating temperature range, max.	100 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Material data**

Material	Polyamide 66	Insulating material	PA
Colour	silver	UL 94 flammability rating	V-2

**System specifications**

Version	for busbar 10 x 3 mm
---------	----------------------

**Additional technical data**

Installation advice	Busbar
---------------------	--------

**Classifications**

ETIM 6.0	EC000001	ETIM 7.0	EC000001
eClass 9.0	27-14-11-46	eClass 9.1	27-14-11-46
eClass 10.0	27-14-11-46	UNSPSC	30-21-18-11

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN, WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>