

SAIBM-M8-4P-(IF)**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Type	SAIBM-M8-4P-(IF)
Order No.	1010090000
Version	Sockets prefabricated to customer spec., M8, Female socket, straight
GTIN (EAN)	4032248715299
Qty.	1 pc(s).

SAIBM-M8-4P-(IF)

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	30 g
------------	------

Temperatures

Operating temperature range, max.	85 °C	Operating temperature range, min.	-25 °C
Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data customisable plug-in connectors

Cable diameter, max.	5.5 mm	Cable diameter, min.	3.5 mm
Coding	none	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.14 mm ²	Connection cross-section, max.	0.5 mm ²
Connection cross-section, min.	0.14 mm ²	Contact surface	Gold-plated
Housing main material	CuZn	Insulation strength	10 ⁸ Ω
Number of poles	4	Plugging cycles	≥ 100
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	30 V
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Screw connection

Standards

Certificate no. (cULus)	E307231
-------------------------	---------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
eClass 9.0	27-44-01-02	eClass 9.1	27-44-01-03
eClass 10.0	27-44-01-02	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN
Engineering Data	WSCAD
User Documentation	Manual