



#### General ordering data

Order No.	1013700000
Part designation	WTR 2.5/D/DRBR
Version	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
EAN	4008190163471
Qty.	25 pc(s).

#### Product notes

Note, ordering data	
Note, technical data	2.5 mm <sup>2</sup> conductor with wire end ferrule with plastic collar only with collar optimised for diameter (order No. 1333100000, 500 pcs)
Product description	Modular disconnect terminals enable circuits to be quickly isolated from the supply so that, for example, maintenance or repair work can be carried out.
Note, accessories	

#### 2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

Solid, min.	0.5 mm <sup>2</sup>
Solid, max.	1.5 mm <sup>2</sup>
Flexible, min.	0.5 mm <sup>2</sup>
Flexible, max.	1.5 mm <sup>2</sup>
Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm <sup>2</sup>
Flexible with ferrule, max. (DIN 46228 pt 1)	1.5 mm <sup>2</sup>

#### Additional technical data

Colour of insulating material	dark beige
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35

**Additional technical data**

Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	W-Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Test-disconnect terminals

**CSA rating data**

Voltage (CSA)	300 V
CSA current	10 A
Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 12

**Conductors for clamping (rated connection)**

Clamping range, min.	0.13 mm <sup>2</sup>
Clamping range, max.	4 mm <sup>2</sup>
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	10 mm
Clamping screw	M 2.5
Blade size	0.6 x 3.5 mm
Tightening torque range	0.4...0.6 Nm
Torque level with DMS electric screwdriver	2
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm <sup>2</sup>
Solid, max.	4 mm <sup>2</sup>
Stranded, min.	1.5 mm <sup>2</sup>
Stranded, max.	4 mm <sup>2</sup>
Flexible, min.	0.5 mm <sup>2</sup>
Flexible, max.	4 mm <sup>2</sup>
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm <sup>2</sup>
Flexible with ferrule, max. (DIN 46228/1)	2.5 mm <sup>2</sup>
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm <sup>2</sup>
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	2.5 mm <sup>2</sup>
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.13 mm <sup>2</sup>
AWG conductor size, max.	3.31 mm <sup>2</sup>

**Dimensions**

Width	5.1 mm
-------	--------

**Dimensions**

Height of lowest version	64.7 mm
Length	60 mm

**Disconnect terminals**

Integral test socket	No
Torque level with DMS electric screwdriver	2

**Rating data**

Rated cross-section	2.5 mm <sup>2</sup>
Rated voltage	500 V
Rated impulse voltage	6 kV
Rated current	14 A
Standards	IEC 60947-7-1
Current with max. conductor	14 A
Pollution severity	3

**UL rating data**

Voltage (UL)	300 V
Current (UL)	10 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 12

**Approvals**

Approvals institutes

**Classifications**

ETIM 2.0	EC000902
ETIM 3.0	EC000902
eClass 4.1	27-14-11-17
eClass 5.0	27-14-11-26
eClass 5.1	27-14-11-26

**Similar products**

Order No.	Part designation	Version
1855610000	WTR 2.5	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, beige, TS 35
1961750000	WTR 2.5 D+ 2STB 6.9/2.3	
1014600000	WTR 2.5 D 2STB 7.5/2.3	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1014700000	WTR 2.5 D 2STB 7.5/2.3	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1964810000	WTR 2.5 D- 2STB 6.9/2.3	
1011120000	WTR 2.5 GE	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, yellow, TS 35

1011130000	WTR 2.5 GN	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, green, TS 35
1011150000	WTR 2.5 GR	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, grey, TS 35
1878530000	WTR 2.5 OR	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, Orange, TS 35
1011140000	WTR 2.5 RT	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Polyamide, red, TS 35
1013000000	WTR 2.5 STB2.0	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1011200000	WTR 2.5 STB2.3	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1011280000	WTR 2.5 STB2.3 BL	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, blue/light blue, TS 35
1011220000	WTR 2.5 STB2.3 GE	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, yellow, TS 35
1011240000	WTR 2.5 STB2.3 RT	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Polyamide, red, TS 35
1011210000	WTR 2.5 STB2.3 SW	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Polyamide, black, TS 35
1011110000	WTR 2.5 SW	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Polyamide, black, TS 35
1013200000	WTR 2.5/D+ STB2.3	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1013600000	WTR 2.5/D-	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1013300000	WTR 2.5/D- STB2.3	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1012900000	WTR 2.5/D/O.TNHE	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1012800000	TR 2.5/O.TNHE STB2.3	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1039900000	WTR 2.5/ZZ	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
1039980000	WTR 2.5/ZZ BL	Disconnect and modular disconnect terminal, 2.5 mm <sup>2</sup> , Screw connection, Wemid, blue/light blue, TS 35
7910180000	WTR 4	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
7910190000	WTR 4 BL	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Screw connection, Wemid, blue, TS 35
7910210000	WTR 4 STB	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Screw connection, Wemid, dark beige, TS 35
7910220000	WTR 4 STB BL	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Screw connection, Wemid, blue, TS 35
1905080000	WTR 4/ZR	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Screw connection, Wemid, dark beige
1905110000	WTR 4/ZR STB	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Wemid, dark beige, TS 35
1905090000	WTR 4/ZZ	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Screw connection, Wemid, dark beige
1905100000	WTR 4/ZZ STB	Disconnect and modular disconnect terminal, 4 mm <sup>2</sup> , Wemid, dark beige, TS 35