

IE-PP-V14P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For protecting your devices against dust and dirt.

General ordering data

Type	IE-PP-V14P
Order No.	1058280000
Version	Plug housing protective cap
GTIN (EAN)	4032248799374
Qty.	10 pc(s).

Creation date April 12, 2020 11:40:42 PM CEST

Catalogue status 03.04.2020 / We reserve the right to make technical changes.

IE-PP-V14P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	35.7 mm	Depth (inches)	1.406 inch
Net weight	4.576 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C		

General data

Colour	black	Housing main material	PA UL 94 V0
Protection degree	IP67	Type of mounting	Indoors only
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
eClass 9.0	27-44-02-08	eClass 9.1	27-44-02-08
eClass 10.0	27-44-02-08		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 9 IETH 18/19 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN