

**Bolt-type screw terminals  
WAH 185/300 BE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

**General ordering data**

Type	WAH 185/300 BE
Order No.	<a href="#">1064760000</a>
Version	Bolt-type screw terminals, Hood, beige, 54 mm
GTIN (EAN)	4008190108267
Qty.	10 pc(s).

**Bolt-type screw terminals**  
**WAH 185/300 BE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	54 mm	Width (inches)	2.126 inch
Height	139 mm	Height (inches)	5.472 inch
Depth	43.9 mm	Depth (inches)	1.728 inch
Net weight	25.5 g		

**Temperatures**

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Material data**

Material	Polyamide 66	Colour	beige
UL 94 flammability rating	V-2		

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on		

**Dimensions**

Pitch in mm (P)	55 mm
-----------------	-------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-27

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>