

**Crimping tool  
HTF HYB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- for C1 contacts
- for D-Sub contact of CM-20 ConCept Module
- IE crimping tool

**General ordering data**

Type	HTF HYB
Order No.	<a href="#">1119580000</a>
Version	Crimping tool, Crimping tool for contacts, 0.08mm <sup>2</sup> , 1mm <sup>2</sup> , FoderBcrimp
GTIN (EAN)	4032248900626
Qty.	1 pc(s).

**Data sheet**

**Crimping tool  
HTF HYB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Weight	438 g	Net weight	443.2 g

**Description of contact**

Crimping range, min.	0.08 mm <sup>2</sup>	Crimping range, max.	1 mm <sup>2</sup>
----------------------	----------------------	----------------------	-------------------

**tool data crimping**

Crimping profile 1, min.	0.08 mm <sup>2</sup>	Crimping type/profile	FoderBcrimp
Crimping profile 1, max.	0.2 mm <sup>2</sup>	Crimping profile 2, min.	0.2 mm <sup>2</sup>
Crimping profile 2, max.	0.5 mm <sup>2</sup>	Crimping profile 3, min.	0.75 mm <sup>2</sup>
Crimping profile 3, max.	1 mm <sup>2</sup>		

**Classifications**

ETIM 3.0	EC001396	ETIM 4.0	EC001396
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	27-11-27-20	eClass 5.1	21-05-08-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue [CAT 9 IETH 15/16 EN](#)

**Data sheet**

**Crimping tool  
HTF HYB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

