

**HDC insert
HDC 24B HP250 MPL4 TYP2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The RockStar[®] HighPower housings are manufactured from high-strength die-cast aluminium and offer perfect protection against harsh environmental conditions thanks to continual optimisation. The multi-part housing gives users the opportunity to examine work processes down to the last step in the workflow.

General ordering data

Type	HDC 24B HP250 MPL4 TYP2
Order No.	1160440000
Version	HDC insert, Number of poles: 4, Size: 8
GTIN (EAN)	4032248947973
Qty.	1 pc(s).

HDC insert HDC 24B HP250 MPL4 TYP2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	140 mm	Length (inches)	5.512 inch
Width	42	Width (inches)	1.654 inch
Height	46 mm	Height (inches)	1.811 inch
Mounting dimension - width	32 mm	Mounting dimension - height	130 mm
Net weight	83.99 g		

Temperatures

Operating temperature, max.	120 °C	Operating temperature, min.	-50 °C
-----------------------------	--------	-----------------------------	--------

General data

Colour	Silver grey	Material	Stainless steel, rust-proof
Series	HighPower		

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
eClass 9.0	27-44-02-92	eClass 9.1	27-44-01-92
eClass 10.0	27-44-02-92		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN
Engineering Data	STEP

HDC insert HDC 24B HP250 MPL4 TYP2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

