

HDC enclosures HDC 16B ADBO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 16B ADBO
Order No.	1209200000
Version	HDC enclosures, Size: 6, Protection degree: IP65, Bulkhead enclosure, Side-locking clamp on upper side, Standard, with cover
GTIN (EAN)	4008190871130
Qty.	1 pc(s).

HDC enclosures HDC 16B ADBO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	115 mm	Length (inches)	4.528 inch
Width	77.3 mm	Width (inches)	3.043 inch
Height	47 mm	Height (inches)	1.85 inch
Mounting dimension - width	103 mm	Mounting dimension - height	32 mm
Net weight	178 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Height of base B1	5.3 mm	Height of housing B	47 mm
Hole pitch length A2	103 mm	Total length housing	93.3 mm
Width base C1	47 mm	Width housing C	43 mm

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection class note	Protection class for this version of cover: IP20
Protection degree	IP65	Surface finish	Powder coating

Version

Clamp version	Side-locking clamp	Cover	with cover
Design	Standard	Design of cover	with cover
Design of housing	Bulkhead enclosure	Design of locking system	Side-locking clamp on upper side
Sealing	NBR	Size	6
Suitable for ModuPlug®	Yes	Top part/bottom part/lid	lower part
Type	Bulkhead (Feed-Through)		

Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-26-12-03	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-44-02-02
eClass 9.1	27-44-02-02		

Approvals

Approvals



ROHS Conform

Data sheet**HDC enclosures
HDC 16B ADBO**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN, WSCAD
Technical Documentation	1209200000 HDC 16B ADBO STP Blatt 1.pdf

Data sheet

**HDC enclosures
HDC 16B ADBO**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

