

HDC enclosures HDC 32B ABU

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 32B ABU
Order No.	1217800000
Version	HDC enclosures, Size: 10, Protection degree: IP65, Open base, Side-locking clamp on lower side, Standard
GTIN (EAN)	4008190148393
Qty.	1 pc(s).

Data sheet

HDC enclosures HDC 32B ABU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	97 mm	Width (inches)	3.819 inch
Height	38 mm	Height (inches)	1.496 inch
Mounting dimension - width	110 mm	Mounting dimension - height	65 mm
Net weight	276 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1, DIBP 84-69-5, Potassium perfluorobutane sulfonate 29420-49-3
------------	--

Dimensions

Height of base B1	7 mm	Height of housing B	38 mm
Hole pitch length A2	110 mm	Total length housing	94 mm
Width base C1	89 mm	Width housing C	82.5 mm

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65
Surface finish	Powder coating	Tightening torque	2 Nm

Version

Clamp version	Side-locking clamp	Design	Standard
Design of housing	Open base	Design of locking system	Side-locking clamp on lower side
Sealing	NBR	Size	10
Suitable for ModuPlug®	Yes	Tightening torque	2 Nm
Top part/bottom part/lid	lower part	Type	Bulkhead (feed-through)

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
eClass 9.0	27-44-02-02	eClass 9.1	27-44-02-02
eClass 10.0	27-44-02-02	UNSPSC	30-21-18-01

Approvals

Approvals



Data sheet**HDC enclosures
HDC 32B ABU**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Technical Documentation	1217800000_HDC_32B_ABU_STP_Blatt_1.pdf

Data sheet**HDC enclosures
HDC 32B ABU**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings