


SwitchMark SM 18/9.5 K MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The new SwitchMark markers have been designed for identifying rotary selector switches from ABB (SM 19/42 K MC) as well as control and signalling devices from Siemens (SM 18/9.5 K MC).

Suitable for:

SM 18/9.5 K MC: Siemens, type 3SB

SM 19/42 K MC: ABB, tag carrier type ONFB72

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

Type	SM 18/9.5 K MC NE GE
Order No.	1248590000
Version	SwitchMark, Device markers, 9.5 x 18 mm, Siemens 3 SB, Yellow
GTIN (EAN)	4050118038958
Qty.	200 pc(s).
compatible printer	1324380000

Data sheet

SwitchMark SM 18/9.5 K MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	18 mm	Width (inches)	0.709 inch
Height	9.5 mm	Height (inches)	0.374 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	0.57 g		

General data

Adhesive	Double-sided adhesive tape	Application/manufacturer	Siemens 3 SB
Colour	Yellow	Material	Polyamide 66
Material colour according to resistance code	4	Operating temperature range	-40...60 °C
UL 94 flammability rating	V-2	Version	Self-adhesive
Width	18 mm		

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-37-12-25	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

Data sheet

**SwitchMark
SM 18/9.5 K MC NE GE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use



Similar to illustration

