

Klippon Klippon POK 7

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Polyester housings The glass fibre-reinforced polyester housings of the Klippon POK series represent a high-quality, inexpensive solution for electric connections. These enclosures are ideal wherever corrosion resistance, shock resistance and a high class of protection are required.

Features:

- 17 sizes
- Cover with stainless steel screws
- fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

Order No.	1277800000
Type	Klippon POK 7
Version	Klippon-Protected component assemblies, Enclosures, Glass fibre-reinforced polyester, 160 mm, 91 mm, 360 mm
GTIN (EAN)	4032248414864
Qty.	1 pc(s).

Klippon Klippon POK 7

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	91 mm	Width	360 mm
Height	160 mm	Mounting dimension - width	340 mm
Mounting dimension - height	110 mm	Weight	2,150 g
Net weight	2,150 g		

Cable glands, right

M12 (2)	11	M16 (2)	6
M20 (2)	4	M25 (2)	2
M32 (2)	2	M40 (2)	1
Side of enclosure	left, top, right, Bottom		

Cable glands, top/bottom

M12	45	M16	36
M20	20	M25	8
M32	6	M40	5
Side of enclosure	left, top, right, Bottom		

General information

Areas of use	Transportation, Harbour facilities, Process industry	UL 94 flammability rating	V-0
Material	Glass fibre-reinforced polyester	Seal material	Chloroprene
Surface finish	untreated	Colour code	RAL 7001
Operating temperature, min.	-40 °C	Operating temperature, max.	100 °C
Impact resistance	7.00 J	Protection degree	IP 66
Enclosure attachment	Holes 6 mm	Cover attachment	M6 slotted and crosshead stainless steel screws

General information on accessories

Material	Glass fibre-reinforced polyester	Mounting dimension - height	110 mm
Mounting dimension - width	340 mm	Surface finish	untreated

horizontal assembly

WDU 10 / ZDU 10	1x29	WDU 16 / ZDU 16	1x24
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x56	WDU 4 / ZDU 4	1x47
WDU 6 / ZDU 6	1x36		

vertical assembly

WDU 10 / ZDU 10 (2)	*	WDU 16 / ZDU 16 (2)	*
WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	*	WDU 4 / ZDU 4 (2)	*
WDU 6 / ZDU 6 (2)	*		

Classifications

ETIM 2.0	EC000058	ETIM 3.0	EC000058
UNSPSC	31-26-15-02	eClass 4.1	27-14-12-06
eClass 5.1	27-14-91-07	eClass 6.2	27-14-91-07
eClass 7.1	27-14-91-07		

Creation date July 9, 2013 2:11:42 PM CEST

**Klippon
Klippon POK 7**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Test certificates**

Certificate No. (MARITREG)	09.04041.250	Certificate no. (cULus)	E223801ROSE
----------------------------	--------------	-------------------------	-------------

Approvals

Approvals



ROHS	Conform
------	---------

Data sheet...

**Klippon
Klippon POK 7**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

