

**THM  
THM EL 24 SI 3L 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the length can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

**General ordering data**

|                    |   |
|--------------------|---|
| Type               | THM EL 24 SI 3L 30M                                   |
| Order No.          | <a href="#">1356520000</a>                            |
| Version            | THM, Device markers, x 24 mm, Silver                  |
| GTIN (EAN)         | 4050118159677   |
| Qty.               | 1 pc(s).  |
| compatible printer | <a href="#">2430920000</a> <a href="#">2448870000</a> |

**THM**  
**THM EL 24 SI 3L 30M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |           |                 |              |
|------------|-----------|-----------------|--------------|
| Length     | 30,000 mm | Length (inches) | 1,181.1 inch |
| Width      | 24 mm     | Width (inches)  | 0.945 inch   |
| Depth      | 0.08 mm   | Depth (inches)  | 0.003 inch   |
| Net weight | 387 g     |                 |              |

**General data**

|                  |                        |                             |              |
|------------------|------------------------|-----------------------------|--------------|
| Adhesive         | Acrylate adhesive      | Approval acc. to UL 969     | Yes          |
| Colour           | Silver                 | Length                      | 30,000 mm    |
| Material         | Polyester              | Number per roll             | 1            |
| Number per sheet | 1                      | Operating temperature range | -40...150 °C |
| Printing method  | Thermotransfer         | UL 94 flammability rating   | V-0          |
| Version          | Endless, Self-adhesive | Width                       | 24 mm        |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001288    | ETIM 6.0   | EC001288    |
| eClass 6.2 | 27-14-91-29 | eClass 7.1 | 27-14-91-29 |
| eClass 8.1 | 27-14-91-29 | eClass 9.0 | 27-40-06-29 |
| eClass 9.1 | 27-40-06-29 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">EPLAN, WSCAD</a>                   |
| Software         | <a href="#">M-Print PRO configuration file</a> |

**Data sheet**

**THM  
THM EL 24 SI 3L 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**Data sheet**

**THM**  
**THM EL 24 SI 3L 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

