

**H2,5/15D BL SP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

- supplied loose in poly-bag
- in multi-pack bag (5 x 100 pcs.)
- Linked of wire-end ferrule strips (50 pcs.)
- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
Order No.	<a href="#">1476280000</a>
Type	H2,5/15D BL SP
GTIN (EAN)	4050118282887
Qty.	100 pc(s).

Creation date January 10, 2023 12:07:30 PM CET

Catalogue status 09.01.2023 / We reserve the right to make technical changes.

**H2,5/15D BL SP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.15 g

**Technical data**

Description of article	Wire end ferrule with plastic collar, blue	Version	Standard

**Wire-end ferrules**

Collar diameter (D2)	4.2 mm	Colour code	DIN
Conductor cross-section	2.5 mm <sup>2</sup>	Contact surface diameter (D1)	2.2 mm
Contact surface length (L2)	8 mm	L1 in mm	15 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 14

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986
Certificate no. (cULus)	E499744

**Downloads**

User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**H2,5/15D BL SP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

