

**cable lug, terminal end  
VFSKHV/1,5-2,5/638**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Fully-insulated tab-connector sleeves made from  
PVC with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

**General ordering data**

|            |   |
|------------|---|
| Type       | VFSKHV/1,5-2,5/638  |
| Order No.  | <a href="#">1491940000</a>  |
| Version    | cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> |
| GTIN (EAN) | 4050118301922   |
| Qty.       | 100 pc(s).  |

## Data sheet

### cable lug, terminal end VFSKHV/1,5-2,5/638

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|        |        |            |        |
|--------|--------|------------|--------|
| Weight | 0.14 g | Net weight | 1.35 g |
|--------|--------|------------|--------|

### Connectors

|                               |                     |                               |                     |
|-------------------------------|---------------------|-------------------------------|---------------------|
| Conductor cross-section, max. | 2.5 mm <sup>2</sup> | Conductor cross-section, min. | 1.5 mm <sup>2</sup> |
| Identification colour         | blue                | Length 1 (l1)                 | 21.5 mm             |
| Material/plastic              | PA                  | Plug-in density (d3)          | 0.8 mm              |
| Plug-in width (d2)            | 6.3 mm              |                               |                     |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001059    | ETIM 6.0   | EC000516    |
| eClass 6.2 | 27-40-02-90 | eClass 7.1 | 27-40-02-04 |
| eClass 8.1 | 27-40-02-12 | eClass 9.0 | 27-40-02-12 |
| eClass 9.1 | 27-40-02-90 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |   |
|--------------------|---|
| Brochure/Catalogue | <a href="#">CAT 9 IETH 15/16 EN</a><br><a href="#">CAT 6 TOOLS 15/16 EN</a> |
|--------------------|---|

**Data sheet**

**cable lug, terminal end**  
**VFSKHV/1,5-2,5/638**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

