

# HDC CONTACTS

## 1543200000

When good enough just isn't good enough

**Weidmüller** 

CS1.6HD E 22-20 SN I1.8

[Email to a Friend](#)

[Sales Information](#)

[Back to StepSearch](#)

[Catalog Home](#)



Representative Photo

### Technical Information

Base material	Copper alloy
Contact Plating	Tin/Lead
Contact Packaging	Contacts, individual
Contacts	stamped
AWG min.	20 AWG
AWG max.	22 AWG

### Additional Data

Cross-section (min.)	0.32 mm (0.01 inches)
Cross-section (max.)	0.5 mm (0.02 inches)
EAN	4008190106102
Type	Pin
Type of connection	Crimped
Volume resistance (small)	3 mOhm
Diameter of insulation (min.)	1.1 mm (0.04 inches)
Diameter of insulation (max.)	1.8 mm (0.07 inches)

### Suggested Accessories

**Product Liability** The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America  
 United States 001 (800) 849-9343  
 Canada 001 (800) 268-4080

or

Weidmüller - Germany  
 Telephone operator 0049 (-5252) 960-0