

**W-Series  
WQB A/24**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	WQB A/24
Order No.	<a href="#">1579000000</a>
Version	W-Series, Cross-connector, For the terminals, Number of poles: 24
GTIN (EAN)	4008 190134211
Qty.	20 pc(s).

**W-Series**  
**WQB A/24**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	123.22 mm	Width (inches)	4.851 inch
Height	23.5 mm	Height (inches)	0.925 inch
Depth	2.5 mm	Depth (inches)	0.098 inch
Net weight	7.18 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., max.	70 °C

**Material data**

Material	tinned copper	Colour	black
----------	---------------	--------	-------

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	24	Rated current, multi-pole	24 A
Type	Cross-connector		

**Dimensions**

Pitch in mm (P)	5.1 mm
-----------------	--------

**Rating data**

Rated voltage	800
---------------	-----

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

**Approvals**

Approvals



ROHS Conform

**Data sheet****W-Series  
WQB A/24**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">18599_WQB_A-24_DXF.dxf</a> <a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>

---