

**W-Series
WQB B/2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WQB B/2
Order No.	1579010000
Version	W-Series, Cross-connector, For the terminals, Number of poles: 2
GTIN (EAN)	4008 190021696
Qty.	50 pc(s).

Creation date August 17, 2020 9:12:22 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

Data sheet

W-Series WQB B/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	10.14 mm	Width (inches)	0.399 inch
Height	23.5 mm	Height (inches)	0.925 inch
Depth	2.5 mm	Depth (inches)	0.098 inch
Net weight	0.56 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	70 °C		

Material data

Material	tinned copper	Colour	black
----------	---------------	--------	-------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	2	Rated current, multi-pole	24 A
Type	Cross-connector		

Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

Rating data

Rated voltage	800
---------------	-----

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS	Conform
------	---------

Data sheet**W-Series**
WQB B/2**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Technical data****Downloads**

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks
