

**Z-series
ZAP/TW 3 OR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	ZAP/TW 3 OR
Order No.	1608820000
Version	Z-series, End plate, Separation plate
GTIN (EAN)	4008190190941
Qty.	50 pc(s).

**Z-series
ZAP/TW 3 OR**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	2 mm	Width (inches)	0.079 inch
Height	78.8 mm	Height (inches)	3.102 inch
Depth	30.5 mm	Depth (inches)	1.201 inch
Net weight	3.721 g		

Temperatures

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

System specifications

Version	End and intermediate plate
---------	----------------------------

Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-33
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-27

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks