

ZBW-6

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image



Our special tools support within the cabinet process in the area of wiring or also the assembly of the components.

General ordering data

Version	Z-series, Operating tool
Order No.	1650700000
Type	ZBW-6
GTIN (EAN)	4008190299378
Qty.	1 pc(s).

ZBW-6

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	23.75 mm	Depth (inches)	0.935 inch
Height	147 mm	Height (inches)	5.787 inch
Width	27.76 mm	Width (inches)	1.093 inch
Net weight	20 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-40
Continuous operating temp., max.	100		

Material data

Material	POM	Colour	orange
UL 94 flammability rating	HB		

System specifications

Version	Operating tool
---------	----------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-04-50-03	ECLASS 12.0	21-04-50-03

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format