

**ZTA 3 ZDU6****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

Version	Accessories, Test adapter, 9 A
Order No.	<a href="#">1654050000</a>
Type	ZTA 3 ZDU6
GTIN (EAN)	4008190420406
Qty.	25 pc(s).

## ZTA 3 ZDU6

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	73.1 mm	Depth (inches)	2.878 inch
Height	31.5 mm	Height (inches)	1.24 inch
Width	8.1 mm	Width (inches)	0.319 inch
Net weight	7.69 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	100		

## Material data

Material	Polyamide 66	Colour	black
UL 94 flammability rating	V-2		

## System specifications

Version	For the terminals	Number of levels	1
Number of clamping points per level	1		

## Additional technical data

Installation advice	Direct mounting	With snap-in pegs	No
---------------------	-----------------	-------------------	----

## Conductors for clamping (rated connection)

Clamping range, max.	1.5 mm <sup>2</sup>	Clamping range, min.	0.5 mm <sup>2</sup>
Number of connections	1	Stripping length	6 mm
Tightening torque, max.	0.3 Nm	Tightening torque, min.	0.3 Nm
Type of connection	Plug-in connection	Wire connection cross section, finely stranded, max.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	1.5 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

## Dimensions

Pitch in mm (P)	5 mm	Height with TS 35	105.5 mm
-----------------	------	-------------------	----------

## General

Installation advice	Direct mounting	Number of poles	1
---------------------	-----------------	-----------------	---

## Rating data

Rated cross-section	1.5 mm <sup>2</sup>	Rated voltage	250 V
Rated current	9 A	Volume resistance according to IEC 60947-7-x	1.83 mΩ
Power loss in accordance with IEC 60947-7-x	0.56 W		

Creation date June 9, 2023 10:01:04 AM CEST

**ZTA 3 ZDU6**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

ETIM 6.0	EC002555	ETIM 7.0	EC002555
ETIM 8.0	EC002555	ECLASS 9.0	27-14-11-48
ECLASS 9.1	27-14-11-48	ECLASS 10.0	27-14-11-48
ECLASS 11.0	27-14-11-48	ECLASS 12.0	27-14-11-48

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	e1c310ef-6b67-4efa-80a6-d307472f4de9

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – 22256_ZTA_3_DXF.dxf</a> <a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	