

**LaserMark
LM MT300 20/8 GE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Type	LM MT300 20/8 GE
Order No.	1686381687
Version	LaserMark, Device markers, 8 x 20.3 mm, yellow
GTIN (EAN)	4008 190493943
Qty.	10 pc(s).

**LaserMark
LM MT300 20/8 GE**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	20.3 mm	Width (inches)	0.799 inch
Height	8 mm	Height (inches)	0.315 inch
Depth	0.08 mm	Depth (inches)	0.003 inch
Net weight	11.4 g		

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	yellow	Halogen	No
Material	Polyester, PVC-free	Material colour according to resistance code	4
Number of markers per packaging unit	2,640	Number per sheet	264
Operating temperature range	-40...150 °C	Printing method	Laser print
UL 94 flammability rating	HB	Version	Self-adhesive
Width	20.3 mm		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29
eClass 10.0	27-40-06-29	UNSPSC	30-21-18-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

Data sheet

**LaserMark
LM MT300 20/8 GE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

