

SKMU EMV PG29**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS EMV (brass locknut - EMC), Locknut, PG 29, 5.7 mm, Brass, nickel-plated
Order No.	1718960000
Type	SKMU EMV PG29
GTIN (EAN)	4008 190352 189
Qty.	15 pc(s).

Creation date February 2, 2023 8:16:38 AM CET

Catalogue status 24.01.2023 / We reserve the right to make technical changes.

SKMU EMV PG29

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	15.733 g
------------	----------

General information

AF size 1	41 mm	Cable glands	PG 29
External thread	PG 29	Halogen	No
Internal thread	PG 29	Length of thread	5.7 mm
Material	Brass, nickel-plated	O.D.	47.36 mm
Pitch of thread	1.59 mm		

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ECLASS 9.0	27-14-44-24
ECLASS 9.1	27-14-44-24	ECLASS 10.0	27-14-44-24
ECLASS 11.0	27-14-44-24	ECLASS 12.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

SKMU EMV PG29

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

