

**GWDR PO (flat gasket - polyethylene)  
GWDR PG16-PO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

**General ordering data**

Type	GWDR PG16-PO
Order No.	<a href="#">1719480000</a>
Version	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 16, Polyethylene
GTIN (EAN)	4008190352745
Qty.	100 pc(s).

## Data sheet

### GWDR PO (flat gasket - polyethylene) GWDR PG16-PO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight	0.23 g
------------	--------

### General information

Cable glands	PG	Diameter of sealing ring	27 mm
External thread	PG 16	Inside diameter D2	22.5 mm
Material	Polyethylene	O.D.	27 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-30 °C
Sealing	PE-HD	Thickness	2 mm

### Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC001181
eClass 9.0	27-43-03-19	eClass 9.1	27-14-44-90
eClass 10.0	27-43-03-19	UNSPSC	31-16-18-18

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**GWDR PO (flat gasket - polyethylene)  
GWDR PG16-PO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

