

**GWDR NP (flat gasket - neoprene)  
GWDR M20-NP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

**General ordering data**

Type	GWDR M20-NP
Order No.	<a href="#">1736240000</a>
Version	GWDR NP (flat gasket - neoprene), Sealing ring, M 20, Neoprene
GTIN (EAN)	4008 190956035
Qty.	50 pc(s).

Creation date May 7, 2020 11:06:17 PM CEST

## Data sheet

### GWDR NP (flat gasket - neoprene) GWDR M20-NP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight	0.356 g
------------	---------

### General information

Material	Neoprene	Cable glands	metric
External thread	M 20	Pitch of thread	1.5 mm
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Thickness	1.2 mm	Inside diameter D2	20 mm
Diameter of sealing ring	24 mm		

### Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
eClass 9.0	27-43-03-19	eClass 9.1	27-14-44-90
eClass 10.0	27-43-03-19	UNSPSC	31-16-18-18

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**GWDR NP (flat gasket - neoprene)**  
**GWDR M20-NP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

