

**GWDR NP (flat gasket - neoprene)
GWDR M25-NP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR M25-NP
Order No.	1736250000
Version	GWDR NP (flat gasket - neoprene), Sealing ring, M 25, Neoprene
GTIN (EAN)	4008 190956042
Qty.	100 pc(s).

Creation date August 6, 2020 7:33:45 PM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

Data sheet

GWDR NP (flat gasket - neoprene) GWDR M25-NP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.32 g
------------	--------

General information

Material	Neoprene	Cable glands	metric
External thread	M 25	Pitch of thread	1.5 mm
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Thickness	1.5 mm	Inside diameter D2	25 mm
Diameter of sealing ring	30 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
eClass 9.0	27-43-03-19	eClass 9.1	27-14-44-90
eClass 10.0	27-43-03-19	UNSPSC	31-16-18-18

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

GWDR NP (flat gasket - neoprene)
GWDR M25-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

