

**VPK EX (Ex blanking plug in plastic)
VP M25-EXE SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



For sealing surplus threaded holes to maintain the IP
class of protection

General ordering data

Type	VP M25-EXE SW
Order No.	1737090000
Version	VPK EX (Ex blanking plug in plastic), Blanking plug, M 25, 15 mm, IP66, IP68, Polyamide
GTIN (EAN)	4008190956561
Qty.	100 pc(s).

VPK EX (Ex blanking plug in plastic) VP M25-EXE SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	20 mm	Length (inches)	0.787 inch
Net weight	5.36 g		

Certificate numbers cable gland

Certificate no. cable gland (ATEX)	LCIE 08 ATEX 6085X	Certificate no. cable gland (IECEx)	IECEx LCI 08.0035X
Identification	Ex e II, Ex tD		

General information

Material	Polyamide	Cable glands	metric
External thread	M 25	Pitch of thread	1.5 mm
Length of thread	15 mm	AF size 1	28 mm
Protection degree	IP54, IP66	Protection degree with GWDR	IP66, IP68
Operating temperature range, min.	-20 °C	Operating temperature range, max.	80 °C
UL 94 flammability rating	V-2	Halogen	No
Note: protection class	IP54 in accordance with EN 60529 standard, minimal without flat gasket; IP66 in accordance with EN 60529, minimal without flat gasket; IP68 in accordance with EN 60529 with flat gasket; Except for 2D application, as specified in the Ex-Certificate, a flat gasket is required for IP66.		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-35
eClass 10.0	27-14-44-25	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

VPK EX (Ex blanking plug in plastic) VP M25-EXE SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

