

**Cable glands
VG M20-EXE SW**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Plastic cable glands for use in ATEX areas

General ordering data

Order No.	1737290000
Type	VG M20-EXE SW
Version	Cable glands, Cable gland, Polyamide, External thread: M 20 x 1.5, Black: RAL 9011
GTIN (EAN)	4008190956769
Qty.	20 pc(s).

**Cable glands
VG M20-EXE SW**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	35 mm	Net weight	8.2 g
--------	-------	------------	-------

Approvals

Approval for cable gland	Ex e II, II 2 GD
--------------------------	------------------

General information

AF size 1	24 mm	Cable gland	metric
Clamp insert	Polyamide	Clamping range, bolted connection , max.	13 mm
Clamping range, min. test adapter	8 mm	Colour code	RAL 9005
External thread	M 20 x 1.5	Length of thread	10 mm
Material	Polyamide	Operating temperature range, max.	80 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Protection degree with GWDR	IP 68	Seal insert	TPE
Torque for cap nut, max.	3 Nm	Torque for cap nut, min.	3 Nm
Torque for connecting adapter, max.	3 Nm	Torque for connecting adapter, min.	3 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 2.0	EC000441	ETIM 3.0	EC000441
UNSPSC	30-21-18-01	eClass 4.1	27-14-12-11
eClass 5.1	27-14-91-11	eClass 6.0	27-14-91-11
eClass 7.0	27-14-91-11		

Approvals

Approvals

