

SlimFix Clip SFC 2/12 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the lengths of 12 mm, 21 mm and 30 mm

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.



General ordering data

Type	SFC 2/12 MC NE WS
Order No.	1758320001
Version	SlimFix Clip, Conductor and cable markers, 3 - 5 mm, 12 x 5.8 mm, white
GTIN (EAN)	4032248019427
Qty.	120 pc(s).
compatible printer	1324380000 2438520000 2438510000

**SlimFix Clip
SFC 2/12 MC NE WS**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	5.8 mm	Width (inches)	0.228 inch
Height	12 mm	Height (inches)	0.472 inch
Depth	7.6 mm	Depth (inches)	0.299 inch
Net weight	0.783 g		

General data

Colour	white	Halogen	No
Material	Polyamide 66	Material colour according to resistance code	9
Operating temperature range	-40...100 °C	Recommended industries	Machinery
Size of labelling field	12 x 5.8 mm	Type of printing	neutral
UL 94 flammability rating	V-2	Width	5.8 mm

Conductor and cable markers

Conductor O.D.	3 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	3 mm	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	3 mm ²	Halogen	No

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
eClass 9.0	27-40-04-01	eClass 9.1	27-40-04-01
eClass 10.0	27-40-04-01	UNSPSC	44-12-17-08

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Product Change Notification	DE - Technische Modifikation MultiCard Material EN - Technical change to MultiCard material Technical change to MultiCard material - DE Technical change to MultiCard material - EN
Software	M-Print PRO configuration file

Data sheet

**SlimFix Clip
SFC 2/12 MC NE WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

