

**VPK (blanking plug in plastic)
VP M16 K54**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP M16 K54
Order No.	1776920000
Version	VPK (blanking plug in plastic), Blanking plug, M 16, 7 mm, IP65, Polyamid 6 (PA6 - GF30)
GTIN (EAN)	4032248156368
Qty.	100 pc(s).

Creation date August 18, 2020 2:18:18 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

**VPK (blanking plug in plastic)
VP M16 K54**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	5.5 mm	Length (inches)	0.217 inch
Net weight	1.6 g		

Temperatures

Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Operating temperature, max.	100 °C	Operating temperature, min.	-40 °C

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-33
eClass 10.0	27-14-44-25	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**VPK (blanking plug in plastic)
VP M16 K54**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

