

**VPMS (blanking plug in brass)
VP M25-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP M25-MS65
Order No.	177750000
Version	VPMS (blanking plug in brass), Blanking plug, M 25, 7 mm, Brass, nickel-plated
GTIN (EAN)	4032248158027
Qty.	100 pc(s).

Creation date August 7, 2020 9:14:21 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

Data sheet

**VPMS (blanking plug in brass)
VP M25-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	11 mm	Length (inches)	0.433 inch
Height	11 mm	Height (inches)	0.433 inch
Net weight	14.26 g	Diameter	28 mm

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General information

Material	Brass, nickel-plated	Cable glands	metric
External thread	M 25	Pitch of thread	1.5 mm
Length of thread	7 mm	Protection degree	IP68 - 5 bar (30 min.)
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Head diameter	28 mm	Halogen	No
O-Ring	NBR	Sealing	NBR

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-33
eClass 10.0	27-14-44-25	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**VPMS (blanking plug in brass)
VP M25-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

