

**GWDR M20-PO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, M 20, Polyethylene
Order No.	<a href="#">1777940000</a>
Type	GWDR M20-PO
GTIN (EAN)	4032248158201
Qty.	100 pc(s).

Creation date February 2, 2023 4:38:26 PM CET

Catalogue status 24.01.2023 / We reserve the right to make technical changes.

## GWDR M20-PO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Technical data

### Dimensions and weights

Net weight	0.2 g
------------	-------

### Temperatures

Operating temperature	-30 °C...90 °C	Operating temperature, min.	-30 °C
Operating temperature, max.	90 °C		

### General information

Cable glands	M 20	Diameter of sealing ring	24 mm
External thread	M 20	Inside diameter D2	20 mm
Material	Polyethylene	Number of wires	1
O.D.	24 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Pitch of thread	1.5 mm
Sealing	PE-HD	Silicone	Yes
Thickness	2 mm		

### Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19	ECLASS 12.0	27-43-03-19

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**GWDR M20-PO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

