

GWDR M25-PO**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, M 25, Polyethylene
Order No.	1777950000
Type	GWDR M25-PO
GTIN (EAN)	4032248158218
Qty.	50 pc(s).

GWDR M25-PO
Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com
www.weidmueller.com
Technical data
Dimensions and weights

Net weight	0.32 g		
------------	--------	--	--

Temperatures

Operating temperature	-30 °C...90 °C	Operating temperature, min.	-30 °C
Operating temperature, max.	90 °C		

General information

Cable glands	M 25	Diameter of sealing ring	29 mm
External thread	M 25	Inside diameter D2	25 mm
Material	Polyethylene	Number of wires	1
O.D.	29 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Pitch of thread	1.5 mm
Sealing	PE-HD	Silicone	Yes
Thickness	2 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19	ECLASS 12.0	27-43-03-19

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

GWDR M25-PO

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings

