

BZT 1 ZA WS 10/5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Accessories, Marker holder
Order No.	1805520000
Type	BZT 1 ZA WS 10/5
GTIN (EAN)	4032248270248
Qty.	100 pc(s).

BZT 1 ZA WS 10/5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	11.7 mm	Depth (inches)	0.461 inch
Height	7.55 mm	Height (inches)	0.297 inch
Width	5.07 mm	Width (inches)	0.2 inch
Net weight	0.224 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-40 °C...100 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	100 °C
Continuous operating temp., min.	-40 °C	Continuous operating temp., max.	100 °C

Material data

Material	Polyamide 66	Colour	dark beige
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

Dimensions

Pitch in mm (P)	5 mm
-----------------	------

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C		

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	CAT 1 TERM 16/17 EN