

Cabtite
CABTITE KEL 24/5**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Cabtite enables you to feed pre-assembled lines through the electrical cabinet wall while maintaining IP54-level protection. As the cable does not have to be split, the manufacturer's guarantee is not invalidated.

General ordering data

| | |
|------------|--|
| Type | CABTITE KEL 24/5 |
| Order No. | 1825940000 |
| Version | Cable entry strips, Cabtite, Plastic, Black, Height: 58 mm, Width: 147 mm, Depth: 17 mm, -40 °C - 140 °C |
| GTIN (EAN) | 4032248328659 |
| Qty. | 10 pc(s). |

Data sheet

Cabtite CABTITE KEL 24/5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 147 mm | Width (inches) | 5.787 inch |
| Height | 58 mm | Height (inches) | 2.283 inch |
| Depth | 17 mm | Depth (inches) | 0.669 inch |
| Net weight | 128.7 g | | |

General information

| | | | |
|-----------------------------------|---------|-----------------------------------|--------|
| Material | Plastic | Operating temperature range, max. | 140 °C |
| Operating temperature range, min. | -40 °C | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000441 | ETIM 4.0 | EC000441 |
| ETIM 5.0 | EC000441 | ETIM 6.0 | EC002624 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-14-92-01 |
| eClass 6.2 | 27-14-92-01 | eClass 7.1 | 27-14-92-01 |
| eClass 8.1 | 27-14-92-01 | eClass 9.0 | 27-14-44-38 |
| eClass 9.1 | 27-18-92-65 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|-------------------------------------|
| Brochure/Catalogue | CAT 5 ENCL 17/18 EN |
| Engineering Data | EPLAN.WSCAD |