


Cabtite
CABTITE KT 4**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Cabtite enables you to feed pre-assembled lines through the electrical cabinet wall while maintaining IP54-level protection. As the cable does not have to be split, the manufacturer's guarantee is not invalidated.

General ordering data

Type	CABTITE KT 4
Order No.	1826470000
Version	Cable grommet, small design, Cabtite, Plastic, Light Grey, Height: 20 mm, Width: 20 mm, Depth: 19 mm, 4.00 - 5.00 mm, -20 °C - 80 °C
GTIN (EAN)	4032248329298
Qty.	10 pc(s).

Data sheet

Cabtite CABTITE KT 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	20 mm	Width (inches)	0.787 inch
Height	20 mm	Height (inches)	0.787 inch
Depth	19 mm	Depth (inches)	0.748 inch
Net weight	8.5 g		

General information

Material	Plastic	Operating temperature range, max.	80 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	5 mm
Outer cable diameter, min.	4 mm		

Classifications

ETIM 3.0	EC000879	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000879
UNSPSC	30-21-18-01	eClass 5.1	27-14-92-01
eClass 6.2	27-14-92-01	eClass 7.1	27-14-92-01
eClass 8.1	27-14-92-01	eClass 9.0	27-14-44-38
eClass 9.1	27-14-44-21		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD