



General ordering data

Order No.	1827260000
Part designation	HDC HB 16 EMVK TSS 1xM32
Version	HDC enclosures, BG: 6, IP 68, Plug, standard, M 32
EAN	4032248332397
Qty.	1 pc(s).

Dimensions

Total length	115.5 mm
Width housing C	53 mm
Height of housing B	80 mm
Hole pitch length A2	0 mm
Cable entry	M 32

General data

Protection class	IP 68
Housing main material	diecast aluminium
Colour	black
Temperature, min.	-40 °C
Temperature, max.	125 °C

Version

Type of housing	Plug Housing
Cable entry	w. threading
Number of cable entry on top	0
Number of cable entry sideways	1
Cover	without cover
Cover	without cover
Size	6
Design	standard
Upper part/Lower part/Cover	Upper part
locking system	M6 screw plug
Cable entry	M 32

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000437
ETIM 3.0	EC000437
eClass 4.1	27-14-08-05
eClass 5.0	27-14-34-19
eClass 5.1	27-14-34-19

Similar products

Order No.	Part designation	Version
1919850000	HDC HB16 EMVK TSS 1M25	HDC enclosures, BG: 6, IP 68, Plug, standard, M 25