

Cabtite
CABTITE KT 25 b

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cabtite enables you to feed pre-assembled lines through the electrical cabinet wall while maintaining IP54-level protection. As the cable does not have to be split, the manufacturer's guarantee is not invalidated.

General ordering data

Type	CABTITE KT 25 b
Order No.	1828040000
Version	Cable grommet, large design, Cabtite, Plastic, Black, Height: 42 mm, Width: 41.5 mm, Depth: 19 mm, 25.00 - 26.00 mm, -20 °C - 80 °C
GTIN (EAN)	4032248333554
Qty.	10 pc(s).

Data sheet

Cabtite CABTITE KT 25 b

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	41.5 mm	Width (inches)	1.634 inch
Height	42 mm	Height (inches)	1.654 inch
Depth	19 mm	Depth (inches)	0.748 inch
Net weight	22.3 g		

General information

Material	Plastic	Operating temperature range, max.	80 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	26 mm
Outer cable diameter, min.	25 mm		

Classifications

ETIM 3.0	EC000879	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000879
UNSPSC	30-21-18-01	eClass 5.1	27-14-92-01
eClass 6.2	27-14-92-01	eClass 7.1	27-14-92-01
eClass 8.1	27-14-92-01	eClass 9.0	27-14-44-38
eClass 9.1	27-14-44-21		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD