

**Cabtite**  
**CABTITE KT 2/5 b****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

Cabtite enables you to feed pre-assembled lines through the electrical cabinet wall while maintaining IP54-level protection. As the cable does not have to be split, the manufacturer's guarantee is not invalidated.

**General ordering data**

Type	CABTITE KT 2/5 b
Order No.	<a href="#">1828140000</a>
Version	Cable grommet, small design, Cabtite, Plastic, Black, Height: 20 mm, Width: 20 mm, Depth: 19 mm, 5.00 - 5.00 mm, -20 °C - 80 °C
GTIN (EAN)	4032248333653
Qty.	10 pc(s).

## Data sheet

### Cabtite CABTITE KT 2/5 b

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	20 mm	Width (inches)	0.787 inch
Height	20 mm	Height (inches)	0.787 inch
Depth	19 mm	Depth (inches)	0.748 inch
Net weight	6.4 g		

### General information

Material	Plastic	Operating temperature range, max.	80 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	5 mm
Outer cable diameter, min.	5 mm		

### Classifications

ETIM 3.0	EC000879	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000879
UNSPSC	30-21-18-01	eClass 5.1	27-14-92-01
eClass 6.2	27-14-92-01	eClass 7.1	27-14-92-01
eClass 8.1	27-14-92-01	eClass 9.0	27-14-44-38
eClass 9.1	27-14-44-21		

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>