

**Z-series
ZAD ZT/ZPS2.5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	ZAD ZT/ZPS2.5
Order No.	1861030000
Version	Z-series, cover plate, yellow, 4.2 mm
GTIN (EAN)	4032248418428
Qty.	25 pc(s).

Z-series
ZAD ZT/ZPS2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	4.2 mm	Width (inches)	0.165 inch
Height	13.7 mm	Height (inches)	0.539 inch
Depth	8.7 mm	Depth (inches)	0.343 inch
Net weight	0.36 g		

Temperatures

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66 GF 30	Colour	yellow
UL 94 flammability rating	HB		

System specifications

Version	cover plate
---------	-------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

Dimensions

Pitch in mm (P)	5 mm
-----------------	------

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
eClass 9.0	27-14-11-33	eClass 9.1	27-14-11-33
eClass 10.0	27-14-11-33	UNSPSC	30-21-18-01

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks