

## IE-PP-V04P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For protecting your devices against dust and dirt.

### General ordering data

Type	IE-PP-V04P
Order No.	<a href="#">1963890000</a>
Version	Plug housing protective cap
GTIN (EAN)	4032248646319
Qty.	10 pc(s).

Creation date August 17, 2020 12:34:04 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

**IE-PP-V04P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	46.7 mm	Depth (inches)	1.839 inch
Net weight	14 g		

**Temperatures**

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C		

**General data**

Colour	black	Housing main material	PA UL 94 V0
Protection degree	IP67	Type of mounting	Indoors only
UL 94 flammability rating	V-0		

**General standards**

Certificate no. (cULus)	E316369
-------------------------	---------

**Classifications**

ETIM 6.0	EC002314	ETIM 7.0	EC002314
eClass 9.0	27-44-02-08	eClass 9.1	27-44-02-08
eClass 10.0	27-44-02-08	UNSPSC	30-21-18-17

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">UL Approval</a> <a href="#">GOST Approval</a>
Brochure/Catalogue	<a href="#">CAT 9 IETH 18/19 EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>

**Data sheet**

**IE-PP-V04P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

