

UV66-ADV-15-IPPC-3022.01

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The IPPC 3000 is a built-in industrial Panel PC equipped with Ultra Low Voltage Intel® Celeron™/ Core™ i-processors.

The robust and durable multi-touch control panels vary from 12.1" to 21.5" and are available with capacitive touchscreen.

The three Ethernet 10/100/1000Mbps ports, two USB 3.0 ports, one USB 2.0 port and one serial interface allow to connect existing and new systems. In addition to the integrated display, the DVI video output enables a supplementary visualization.

The IPPC 3000 series comprises two configuration variants that can be selected according to requirements: Intel Celeron™ 3765U 1.9GHz Dual Core with 4GB RAM and 60GB SSD hard drive or Intel Core™ i5-5350U 1.8GHz Dual Core with 8GB RAM and 120GB SSD hard drive.

Both variants come with the operating system Windows 10 IoT Enterprise 2019.

General ordering data

Version	Industrial Panel-PC, Display size 15.6", Capacitive touch, MultiTouch, Front protection IP66
Order No.	2676540000
Type	UV66-ADV-15-IPPC-3022.01
GTIN (EAN)	4050118706079
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2023-03-31

UV66-ADV-15-IPPC-3022.01

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General data

Current consumption	Voltage	24 V
	Current	2.08 A
Operating system	Windows 10 IoT Enterprise LTSC 2019 64bit	
Protection degree	IP66	
Voltage supply	24 V DC (18-32 V DC) isolated	

Dimensions and weights

Depth	83 mm	Depth (inches)	3.268 inch
Height	280.5 mm	Height (inches)	11.043 inch
Width	433 mm	Width (inches)	17.047 inch
Wall thickness, min.	2 mm	Wall thickness, max.	6 mm
Net weight	4,900 g		

Temperatures

Storage temperature	-20 °C ... +60 °C	Operating temperature	0 °C ... +50 °C
Humidity	80 % relative humidity (without condensation)		

Equipment

Angle (horizontal)	Left: 85° / Right: 85°	Angle (vertical)	Top: 80° / Bottom: 80°
Luminance	400 cd/m ²	Material display	Glass
Material frame	Aluminium	Number of displayable colours	16 M
Resolution	1366 x 768	Size	15.6"
Touch-Screen	capacitive, MultiTouch		

System data

Interfaces behind	3x Ethernet 10/100/1000 MBit/s (RJ45), 2x USB 3.0, 1x USB 2.0, 1x DVI-I, 1x RS232 (DB9M)	Memory	120 GB mSATA SSD
Memory (RAM)	8 GB, DDR3	Operating system	Windows 10 IoT Enterprise LTSC 2019 64bit
Processor	Intel® Core™ i5-5350U - Dual Core 1.8 GHz (2.9 GHz Turbo)		

Classifications

ETIM 6.0	EC001414	ETIM 7.0	EC001414
ETIM 8.0	EC001414	ETIM 9.0	EC001414
ECLASS 9.0	19-20-01-03	ECLASS 9.1	19-20-01-03
ECLASS 10.0	19-20-01-03	ECLASS 11.0	19-20-01-03
ECLASS 12.0	19-20-01-03	ECLASS 13.0	19-20-01-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	c67eaff0-dbf6-4589-ba08-8f513fc6ba7f

Creation date March 12, 2024 6:07:46 PM CET

Catalogue status 09.03.2024 / We reserve the right to make technical changes.

2

UV66-ADV-15-IPPC-3022.01

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity - UV66-XXX-XX-IPPC-30XX.XX
Engineering Data	CAD data – STEP
User Documentation	QGUI UV66 IPPC30XX
Catalogues	Catalogues in PDF-format


UV66-ADV-15-IPPC-3022.01

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com


Drawings

Maße (mm) / Dimensions (mm)




	LCD	A	B	C	D	E
UV66-ADV-12-IPPC-3001.01	12.1"	331	234	41	22	5
UV66-ADV-15-IPPC-3001.01	15.6"	433	280.5	41	36	6
UV66-ADV-18-IPPC-3001.01	18.5"	503	320.5	41	35	6
UV66-ADV-21-IPPC-3001.01	21.5"	581.5	367.5	41	35	8
UV66-ADV-12-IPPC-3022.01	12.1"	331	234	41	22	5
UV66-ADV-15-IPPC-3022.01	15.6"	433	280.5	41	36	6
UV66-ADV-18-IPPC-3022.01	18.5"	503	320.5	41	35	6
UV66-ADV-21-IPPC-3022.01	21.5"	581.5	367.5	41	35	8

Montageausschnitt / Panel cut-out



	LCD	E (mm)	F (mm)
UV66-ADV-12-IPPC-3001.01	12.1"	313	218
UV66-ADV-15-IPPC-3001.01	15.6"	410	255
UV66-ADV-18-IPPC-3001.01	18.5"	480	300
UV66-ADV-21-IPPC-3001.01	21.5"	559	346
UV66-ADV-12-IPPC-3022.01	12.1"	313	218
UV66-ADV-15-IPPC-3022.01	15.6"	410	255
UV66-ADV-18-IPPC-3022.01	18.5"	480	300
UV66-ADV-21-IPPC-3022.01	21.5"	559	346

Montageabstände / Mounting distances



X	Y	Z
> 50 mm	> 100 mm	> 50 mm

Industrial panel PC (IPPC) 3000 series

