

**IE-SFP-10GE-MM-03****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Features of SFP-Transceiver series**

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

**General ordering data**

Version	SFP+ transceiver, 10 Gbps, Multimode, LC-Duplex, 0.3 km, -40 °C...85 °C
Order No.	<a href="#">2779110000</a>
Type	IE-SFP-10GE-MM-03
GTIN (EAN)	4064675048473
Qty.	1 pc(s).

Creation date December 4, 2023 1:19:51 PM CET

Catalogue status 24.11.2023 / We reserve the right to make technical changes.

**IE-SFP-10GE-MM-03****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	17.5 g
------------	--------

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
---------------------	----------------	-----------------------	----------------

**EMC conformity and approvals**

EMC standards	EN 55032, EN 55035	Safety standard	UL 62368-1
---------------	--------------------	-----------------	------------

**Environmental conditions**

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C

**Fibre optic transceiver characteristics**

Transmission rate	10 Gbps		
Digital diagnostic monitor function (DDM)	Supported		
Transceiver type	Multimode		
Connector type	LC-Duplex		
Transmission distance, typ.	0.3 km		
Wavelength	typ.	850 nm	
	Wavelength	TX	
	min.	840 nm	
	max.	860 nm	
	Wavelength	RX	
	min.	840 nm	
Receive power	min.	-9.9 dBm	
	max.	-1 dBm	
Transmission power	min.	-6.5 dBm	
	max.	-1 dBm	
Link-budget	3.4 dB		

**Guarantee**

Time interval	3 years
---------------	---------

**Power supply**

Voltage supply	3.3 V (via Ethernet switch)
----------------	-----------------------------

**Technical data**

Type of mounting	Insert in SFP slot
------------------	--------------------

## IE-SFP-10GE-MM-03

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Technical data

### Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC003628	ETIM 9.0	EC003628
ECLASS 9.1	27-44-02-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	19-17-03-03	ECLASS 12.0	19-17-03-03
ECLASS 13.0	19170303		

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a> <a href="#">RCM Declaration of Conformity</a> <a href="#">UK Declaration of Conformity</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>