

**WAVEBOX
TOP UNIT L 17.5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Do not use product for new
developments**



Modular electronics housing, 17.5 mm wide with 4 No.
3-pole 2-tier plug-in connections (screw and tension
clamp). Height of enclosure: 112 mm

General ordering data

Delivery status	This article will no longer be available in the future.
Available until	2018-12-31
Type	TOP UNIT L 17.5
Order No.	8426580000
Version	Electronics housings, WAVEBOX , Head, Width: 17.5 mm
GTIN (EAN)	4032248037681
Qty.	10 pc(s).

**WAVEBOX
TOP UNIT L 17.5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	92.4 mm	Length (inches)	3.638 inch
Width	17.5 mm	Width (inches)	0.689 inch
Height	112.4 mm	Height (inches)	4.425 inch
Net weight	9.2 g		

System characteristics

Version	Head	Number of connection levels	2
Protection degree	IP20		

Material data

CTI	≥ 175	UL 94 flammability rating	V-0
Storage temperature, min.	-25 °C	Storage temperature, max.	55 °C
Max. relative humidity during storage	80 %	Operating temperature, min.	-50 °C
Temperature range, installation, min.	-25 °C		

Classifications

ETIM 3.0	EC001284	ETIM 5.0	EC002643
UNSPSC	30-21-18-01	eClass 6.2	27-26-11-01
eClass 7.1	27-44-04-01	eClass 8.1	27-44-04-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [FL ANALO.SIGN.CONV. EN](#)
[MB DEVICE MANUF. EN](#)
[FL MACHINE SAFETY EN](#)
[FL 72H SAMPLE SER EN](#)
[PO OMNIMATE EN](#)