

IE-FM6D2UE0002MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5, 6 and 14
- consistently Cat. 6_A with **STEADYTEC**® technology
- in IP20 and IP67
- all relevant industrial connections: RJ45, SC, ...
- comprehensive range of accessories

General ordering data

Version	Dragline cable, ST IP 20, ST IP 20, 62.5 µm, PUR, 2 m
Order No.	8876460020
Type	IE-FM6D2UE0002MST0ST0X
GTIN (EAN)	4050118699067
Qty.	1 pc(s).

Creation date December 4, 2023 12:11:07 PM CET

Catalogue status 24.11.2023 / We reserve the right to make technical changes.

IE-FM6D2UE0002MST0ST0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	2 m	Length (inches)	78.74 inch
Net weight	74 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

Cable structure

Cable layout	Break-out dragline	Core diameter	62.5 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

Mechanical and material properties of cable

Bending cycles	100,000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	77 mm		

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ECLASS 9.0	27-06-10-03	ECLASS 9.1	27-06-10-03
ECLASS 10.0	27-06-10-03	ECLASS 11.0	27-06-10-03
ECLASS 12.0	27-06-10-03	ECLASS 13.0	27061003

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--